

## SITA CleanoSpector

Contact-free cleanliness inspection of part surfaces New Features — Updated Design



- √ Faster measurement
- √ Updated design
- √ Shortcut key to device check with standards
- √ Adjustable brightness of target pointer
- ✓ Automatic re-start of target pointer after measurement
- ✓ Mute mode
- ✓ Extensive accessories

# SITA CleanoSpector

#### **Accessories**

#### **Contact-free measurement**

#### Fine adjustment knob

Convenient fine adjustment of measurement distance for contact-free measurement with stand (e.g. on small parts or in tiny grooves)



#### **Measurement with spacers**

### Additional spacers for easy measurement at various part geometries

e.g. wires, pipes, grooves

#### Different spacer materials

Stainless steel: robust and easy to clean Plastic: for sensitive parts



#### **Handling of parts**

#### V-block

Convenient and solid fixing of rotation-symmetric components



#### **Checking**

#### **Calibration standards**

Set of calibration standards for calibration of the device directly on-site



#### Cleaning

#### **Cleaning Kit**

Complete equipment for cleaning of the sensor optics



#### Contact

SITA Messtechnik GmbH Gostritzer Straße 63 01217 Dresden Germany Tel.: +49 (0)351 8 71 8041 Fax: +49 (0)351 8 71 8464 info@sita-process.com www.sita-process.com