

Model FP 115 | Drying and heating chambers with forced convection and program functions

A BINDER material test chamber with mechanical convection of the FP series provides reliably short drying times and particularly fast heating – even for chambers under full loads.

BENEFITS

- Uniform drying conditions thanks to APT.line™ technology
- Identical test conditions throughout the chamber interior independent of sample size and quantity
- Outstanding thermal insulation saves operation costs
- Advanced programming options





Model 115

Model 115

MAIN FEATURES

- Temperature range: +10 °C above ambient temperature up to +300 °C
- High temperature accuracy thanks to APT.line[™] technology
- Adjustable fan speed
- · Controller with interval and real-time programming
- Electromechanical control of the exhaust air flap
- 2 chrome-plated racks

• Units up to 115 liters are stackable

- Class 2 independent adjustable temperature safety device (DIN 12880) and class 3.1 independent temperature safety device (DIN 12880) with visual/acoustic alarm available for selection on the controller
- Ergonomic handle design
- Computer interface: Ethernet
- Internal data logger, measured values can be read out in open format via USB

ORDERING INFORMATION

Interior volume [L]	Voltage	Option model	Version	ArtNo.
	230 V 1~ ph 50/60 Hz	Standard	FP115-230V	9010-0364
116	120 V 1~ ph 60 Hz	Standard	FP115UL-120V	9010-0368



TECHNICAL DATA

Description	FP115-230V ¹	FP115UL-120V ¹
Article Number	9010-0364	9010-0368
Performance Data Temperature		
Temperature range +10 °C above ambient temperature to [°C]	300	300
Temperature variation at 150 °C [± K]	1.4	1.4
Temperature fluctuation at 150 °C [± K]	0.3	0.3
Heating-up time to 150 °C [min]	19	19
Recovery time after 30 seconds door open at 150 °C [min]	5	5
Tabellen		
Air change (approx.) at 100 °C [x/h]	32	32
Electrical data		
Rated Voltage [V]	230	120
Power frequency [Hz]	50/60	60
Nominal power [kW]	1.4	1.4
Unit fuse [A]	10	16
Phase (Nominal voltage)	1~	1~
Measures		
Interior volume [L]	116	116
Net weight of the unit (empty) [kg]	62	62
Permitted load [kg]	150	150
Load per rack [kg]	30	30
Wall clearance back [mm]	160	160
Wall clearance sidewise [mm]	100	100
Internal Dimensions		
Width [mm]	550	550
Height [mm]	550	550
Depth [mm]	383	383
Doors		
Unit doors	1	1
Housing dimensions not incl. fittings and connections		
Width net [mm]	710	710
Height net [mm]	732	732
Depth net [mm]	636	636
Environment-specific data		
Sound-pressure level [dB(A)]	43	43
Fixtures		
Number of shelves (std./max.)	2/5	2/5

1 All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

OPTIONS

Designation	Description	*	ArtNo.
	left		
	30 mm	01	8012-2210
	50 mm	01	8012-2213
	100 mm	01	8012-2207
	right		
Access port with silicone	10 mm	01	8012-2206
	30 mm	01	8012-2212
plug	50 mm	01	8012-2215
	100 mm	01	8012-2209
	top		
	10 mm	01	8012-2199
	30 mm	01	8012-2211
	50 mm	01	8012-2214
	100 mm	01	8012-220
Analog output 4-20 mA	for temperature values (output not adjustable)	02	8012-2188
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	_	8012-2231
	for temperature, measurement in center of chamber at specified temperature	-	8012-222
Calibration certificate,	temperature measurement incl. certificate and 27 measuring points at specified temperature	-	8012-222
temperature	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	-	8012-2228
	temperature measurement incl. certificate, 9 measuring points at specified temperature	-	8012-2230
Door gasket	made of FKM, silicone-free	-	8012-2234
Door lock	lockable door handle	-	8012-2237
Gas-tight option model	Incl. additional measures for the greatest possible impermeability to gas; not in conjunction with access port or interior lighting option	_	8012-2217
HEPA air filter	On fresh air supply for unit; filter classification H14 (acc. to. EN 1822-1:2009, > 99.995% at 0.3 µm); not in conjunction with reinforced heating output, reinforced fan	-	8012-2220
Inert gas connection	With gas inlet and outlet, Ø 10 mm, incl. additional measures for the greatest possible impermeability to gas; not in conjunction with access port or interior lighting option	-	8012-2196
Inner chamber, reinforced	max. total load 170 kg	_	8012-222
	with 15 W light bulb		
nterior lighting	120 V option model	-	8012-218
	230/240 V option model	-	8012-2190
Measurement of air exchange rate	in accordance with ASTM D5374, definition and protocol according to ambient temperature	-	8012-223
Pt 100 temperature sensor	additional flexible Pt 100, interior, for displaying the temperature on the unit display	-	8012-2193
* Notes > See last nage			

* Notes > See last page

ACCESSORIES

Designation	Description	*	ArtNo.
APT-COM™ 4 BASIC-	for simple logging and documentation requirements with up to 5 networked units.		
Edition	version 4, BASIC edition	-	9053-0039
APT-COM™ 4 GLP-	for working under GLP-compliant conditions. Measured values are documented in a tamper-proof way in line with the requirements of FDA Regulation 21 CFR 11.		
Edition	version 4, GLP edition	-	9053-0042
APT-COM™ 4	convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.		
PROFESSIONAL-Edition	version 4, PROFESSIONAL edition	-	9053-0040
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	-	8012-2250
Notos Soo last pago			

* Notes › See last page



Data Sheet Model FP 115

BINDER

Designation	Description	*	ArtNo.
	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit		
	Digital in PDF format	-	7057-000
	Hard copy inside folder	-	7007-000
Qualification documents	$IQ/OQ/PQ$ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ ; parameters: temperature, CO_2 , O_2 – or pressure, depending on unit		
	Digital in PDF format	-	7057-000
	Hard copy inside folder	-	7007-000
	chrome plated	-	8012-204
Rack	stainless steel	-	8012-2168
Rack accessories	fasteners (1 set of 4) for additional security of racks	-	8012-0531
Rubber pads	set anti-slip feet	-	8012-203
Shelf, perforated	Stainless steel	-	8012-2176
Table on castors	stable cart, casters with locking brakes, dimensions: W 1,000 x D 800 x H 780 mm	-	9051-0018
* Notes > See last nage			

* Notes > See last page

SERVICES

Designation	Description	*	ArtNo.
Installation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	05	DL10-0100
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	05	DL10-0500
Maintenance contracts			
Maintenance services			
BRONZE 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	05	DL20-0710
GOLD 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate	05	DL20-0910
Maintenance	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	05	DL20-020
SILVER 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	05	DL20-0810
Calibration services			
Colibustion costificate to management	Calibration of one (1) test temperature specified by the user in center of chamber, including certificate	03, 04, 05	DL30-0101
Calibration certificate, temperature	Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate	03, 04, 05	DL30-0102
Measurement of air exchange rate	including certificate (in accordance with ASTM D5374)	03, 04, 05	DL33-000
Temperature measurement, 18 measuring points	Temperature measurement with 18 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-0118
Temperature measurement, 27 measuring points	Temperature measurement with 27 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-0127
Temperature measurement, 9 measuring points	Temperature measurement with 9 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-0109

* Notes > See last page

Data Sheet Model FP 115

BINDER

Description	*	ArtNo.
Execution of IQ/OQ in accordance with qualification folder	05	DL41-0200
Execution of IQ/OQ/PQ in accordance with qualification folder	05	DL44-0500
The warranty is extended by 1 year from the delivery date, wear parts are excluded	-	DL50-0010
	Execution of IQ/OQ in accordance with qualification folder Execution of IQ/OQ/PQ in accordance with qualification folder	Execution of IQ/OQ in accordance with qualification folder 05 Execution of IQ/OQ/PQ in accordance with qualification folder 05

* Notes > See last page



NOTES

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge. UL mark is not granted when this option is used. 01
- 02
- Sensor calibration is performed in an accredited calibration laboratory. 03
- Calibration is performed according to the BINDER factory standard. 04
- 05 Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

BINDER GmbH

Tuttlingen, Germany TEL +49 7462 2005 0 FAX +49 7462 2005 100 info@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 FAX +852 39070507 asia@binder-world.com www.binder-world.com

BINDER Environmental Testing

Equipment (Shanghai) Co., Ltd. Shanghai, P.R. China TEL +86 21 685 808 25 FAX +86 21 685 808 29 china@binder-world.com www.binder-world.com

Representative Office for CIS

Moscow, Russia TEL +7 495 988 15 16 FAX +7 495 988 15 17 russia@binder-world.com www.binder-world.com

BINDER Inc.

Bohemia, NY, USA TEL +1 631 224 4340 FAX +1 631 224 4354 usa@binder-world.com www.binder-world.us